

Sprunlace Нетканые салфетки [SMT Трафарет для чистки салфеток в рулоне](#)

## Товар подробности

материал	55% древесная 45% полиэстер
Размер	530мм * 400мм * 10м
цвет	белый
Вес	56gsm
ядро	пластик или же бумага
Образец	Свободно
МОQ	50 роллы
порт	Шанхай

### Особенность

1. Esocoо изготовлен из высококачественного нетканого материала из полиэфирной целлюлозы
2. Первичная очистка
3. Отличное поглощение водой и растворителем
4. Без ворса и без царапин на поверхности принтера

### заявка

Он может использоваться для всех автоматических печатных машин, таких как MPM, DEK, KME, YAMAHA, MINAMI, JUKI, EKRA, ERT, FUJI, SANYO и др.

**Sprunlace Нетканые салфетки [SMT Трафарет для чистки салфеток в рулоне](#)**







# YICHEN

DIGITAL PRODUCTS FACTORY



Our Team



Factory





## Trade Assurance

**TRADE WITH CONFIDENCE,  
CREDIBLE AND RELIABLE**

Your payment is protected 100% of the Trade Assurance Order Amount if the product quality is not to your satisfaction or if the order is not shipped on time.





#### About customer service

If your inquiry didn't be replied in time, maybe because of large amount of consulting, please wait patiently, or maybe system problems, your inquiry was lost etc. If the time is too long, Please contact other lights on customer service, or login back Wangwang, then consult, please forgive any inconvenient by this.



#### About after-sale

In the process of selling, if clients find quality problems in products, clients can note us, we'll take great care in performing this matter, the cost paid by us; if we find serious quality problems and can't be remedy, clients have right to return quality problems products to us, we must return the cost of the products.



#### About shipping

Sample lead time: 1-3 days; Mass order production: 7-12 days or negotiated . (By air or by sea depends on clients' choice)



**Tel:** 86-512-50313419  
**Mob:** 86-15895659543  
**Fax:** 86-512-57336236  
**Email:** yc@yichenwipe.cn

[Contact Us](#)

[Go to the home](#)

**WELCOME TO VISIT OUR FACTORY!**