# Sottostencil ad alta assorbente SMT Pulizia salviette

## Dettagli prodotto:

Materiale	55% legno + 45% poliestere
Peso	56gsm
Dimensione	Come la vostra richiesta
Tipo	Roll
Utilizzo	Decrittografia, FUJU e così via
Esempio	Campione gratuito
Certificazione	ISO9001, SGS, RoHS
Porta	Shanghai

## **Caratteristica:**

- 1. generazione bassa della particella
- 2. nessuna sostanza estraibile
- 3. Alta assorbente
- 4. purezza e morbidezza eccellenti
- 5. Strong e durevole
- 6. vari formati e modelli sono disponibili

# **Applicazione:**

Le salviette sono particolarmente utilizzati nella pulizia stencil, stagno ridondante su circuito per mantenere il bordo Immacolata in fabbrica elettronica SMT.

Tipo: rotolo o lamiera

Nucleo: nuclei di carta e plastica, con tacca o non

## SMT alta assorbente sottostencil pulizia salviette






























### About customer service

If your inquiry didn't be replied in time, maybe because of large amount of consulting, please wait patiently, or maybe system problems, your inquiry was lost etc. If the time is too long, Please contact other lights on customer service, or login back Wangwang, then consult, please forgive any inconvenient by this.



#### About after-sale

In the process of selling, if clients find quality problems in products, clients can note us, we'll take great care in performing this matter, the cost paid by us; if we find serious quality problems and can't be remedy, clients have right to return quality problems products to us, we must return the cost of the products.



#### About shipping

Sample lead time: 1-3 days; Mass order production: 7-12 days or negotiated . (By air or by sea depends on clients' choice)



Tel: 86-512-50313419 Mob: 86-15895659543 Fax: 86-512-57336236 Email: yc@yichenwipe.cn

Contact Us

Go to the home

WELCOME TO VISIT OUR FACTORY!